

RoMoControl


Efficiency in Rotomolding



No cooling
packs
necessary!

Recording of process data

- :: optimisation of heating/
cooling phase
- :: reduction of rejects
- :: shortening the running-in period
- :: increasing the productivity
- :: easy certification of products
- :: testing the oven sensor system
- :: online monitoring and docu-
mentation of the process



monitoring and documentation
software - RoMoSoft

Technical Data

dimensions: 290 x 330 x 350 mm (H x W x L)

16 available temperature sensors
(0-350 °C/± 2 °C) e.g.: oven, mould, IAT
(multiple at once)

2 pressure sensors (± 350 mbar ≈ ± 5 psi)

12 cycles (20 min at 300 °C) without cool-
ing (no cooling packs necessary!)

accumulator operating about many month

protection class: IP 65

**Institut für Polymer- und
Produktionstechnologien e.V.**

Affiliated institute of Hochschule Wismar

- fon (+49) 03841 758 23 90
- fax (+49) 03841 758 23 99
- web www.ipt-wismar.de
- mail info@ipt-wismar.de

Alter Holzhafen 19 · 23966 Wismar



ipt²

INSTITUT FÜR POLYMER- UND
PRODUKTIONSTECHNOLOGIEN E.V.
An-Institut der Hochschule Wismar